

I/O PORT DIP SWITCH SETTINGS
(FOR TCR-100 AND ORIGINAL TCR-200 BOARDS)

The TCR-100 series card, as well as the original TCR-200 card, used an 8-position DIP switch for I/O port configuration. TCR-100/200 software supports I/O port address 300, 310, 320, and 330. To configure one of the four addresses, use the follow truth table:

1 = ON/CLOSED 0 = OFF/OPEN

SW	1	2	3	4	5	6	7	8
300	1	1	1	1	1	1	0	0
310	1	1	0	1	1	1	0	0
320	1	1	1	0	1	1	0	0
330	1	1	0	0	1	1	0	0